

ООО "ЛАНФОР РУС"
195112, г. Санкт-Петербург,
пр. Малоохтинский, д. 68
Тел/факс: +7 (812) 309-05-12
+7 (499) 703-20-73
+7 (343) 236-63-20
E-mail: zakaz@lanfor.ru
<http://www.lan-for.ru>

PosiTest DFT

Coating Thickness Gage

Instruction Manual ver. 3.0



Combo: measures on all metals. The letter "F" (ferrous, e.g. steel) or "N" (non-ferrous, e.g. aluminum) is displayed with each reading depending on the substrate. Gage automatically recognizes the substrate.

Ferrous: measures on steel only. The letter "F" is always displayed.

Operation

Automatic power up when probe is depressed. Power down after 30 seconds on no activity.

Place flat on surface. Hold steady. When measurement is obtained, new reading flashes and gage beeps. Lift gage.

Measurement Units

Press and HOLD both buttons for 5 seconds to convert from mils to microns or vice versa.

Zeroing

Press and release both buttons simultaneously. The display blinks "0". Measure the uncoated part. Zeroing provides best coating thickness accuracy.

1 Point Calibration Adjustment

Also known as 'Offset' or 'Correction Value'. Measure a known thickness such as a shim. To adjust, press and release both buttons 2 times and adjust the reading Up (Right button) or Down (Left button) until the expected thickness is displayed. Press both buttons to set.

Factory calibration adjustments can be restored anytime by performing a Reset.

Reset

Press and release both buttons 3 times to restore the factory zero setting. Handy when an uncoated part is not available for zeroing.

Moving Average

Press Left button to display number of readings. Release to display the average of up to the last 10 measurements. To clear, hold Left button for 3 seconds. Moving Average is RESET when powered off.


Flip Display

Press Right button to rotate the display.

Shims

Shims provide a quick operational check. Also used for protection on tacky, rough or hot surfaces.

AAA Alkaline Battery

Replace when  stays on LCD.

Range:	0-40 mils	0-1000 μm
Accuracy:	+/- (0.1 mils + 3%)	+/- ($2\mu\text{m}$ + 3%)

DeFelsko's sole warranty, remedy and liability are the express limited warranty, remedy, and limited liability that are set forth on its website: www.defelsko.com/terms